

# LKEH-202FEUL-RG Cut Sheet



Patlite LED signal tower, (2) tiers, 100mm diameter, red/green, permanent or flashing (60 fpm +/- 3 fpm) light function, (32) alarms, 24 VDC, NPN polarity, colored lens, 325.3mm body length, light gray, 360 degree viewing angle, direct mount, IP53.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LKEH-202FEUL-RG>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Signal tower
<b>Bulb Type</b>	LED
<b>Number of Pre-Assembled Tiers</b>	2
<b>Diameter</b>	100mm
<b>Light Color(s)</b>	Red/green
<b>Light Function</b>	Permanent or flashing (60 fpm +/- 3 fpm)
<b>Number of Alarms</b>	32
<b>Voltage Rating</b>	24 VDC
<b>Polarity</b>	NPN
<b>Lens Type</b>	Colored
<b>Body Length</b>	325.3mm
<b>Body Color</b>	Light gray
<b>Body Material</b>	AES plastic
<b>Tower Viewing Angle</b>	360 degree
<b>Loudness Decibel</b>	105 dB at 1m
<b>Tone Frequency</b>	293 Hz
<b>Tone Type</b>	(32) selectable
<b>Touch to Acknowledge</b>	No
<b>Connector Type</b>	Pigtail
<b>Mounting</b>	Direct
<b>IP Rating</b>	IP53

## Agency Approvals

<b>UL Listed File #</b>	E215660
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	NONE
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>