

LKEH-302FEUL-RYG Cut Sheet



Patlite LED signal tower, (3) tiers, 100mm diameter, red/amber/green, permanent or flashing (60 fpm +/- 3 fpm) light function, (32) alarms, 24 VDC, NPN polarity, colored lens, 385.4mm body length, light gray, 360 degree viewing angle, direct mount, IP53.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LKEH-302FEUL-RYG>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number of Pre-Assembled Tiers	3
Diameter	100mm
Light Color(s)	Red/amber/green
Light Function	Permanent or flashing (60 fpm +/- 3 fpm)
Number of Alarms	32
Voltage Rating	24 VDC
Polarity	NPN
Lens Type	Colored
Body Length	385.4mm
Body Color	Light gray
Body Material	AES plastic
Tower Viewing Angle	360 degree
Loudness Decibel	105 dB at 1m
Tone Frequency	293 Hz
Tone Type	(32) selectable
Touch to Acknowledge	No
Connector Type	Pigtail
Mounting	Direct
IP Rating	IP53

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document