

LLR-C23PA-NMK-400 Cut Sheet



Contrinex photoelectric sensor, rectangular, ABS plastic housing, through-beam emitter, visible red light emission, 25m sensing distance, 10-30 VDC operating voltage, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LLR-C23PA-NMK-400>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	20 x 10 x 30mm
IP Rating	IP67
Housing Material	ABS plastic
Sensing Method	Through-beam emitter
Operating Voltage	10-30 VDC
Number of Wires	3
Sensing Distance	25m
Sensitivity	IO-Link only
Switching Frequency	1 kHz
Light Emission	Visible red

IO-Link Compatible	Yes
Cable Length	6.5ft/2m
Jacket Material	Carbon steel
Connection	Pigtail
Communication Port and Connection Type(s)	(1) 4-wire pigtail (IO-Link) port(s)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM2
IO-Link Version	IO-Link v1.0
Standard I/O Mode Supported	Yes
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LLR-C23PA-NMK-400.pdf>
See store item page for other formats.