

LLR-C23PA-NMS-101 Cut Sheet



Contrinex photoelectric sensor, rectangular, ABS plastic housing, through-beam receiver, visible red light emission, 25m sensing distance, 10-30 VDC operating voltage, complementary light-on/dark-on, NPN, 4-wire, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LLR-C23PA-NMS-101>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	20 x 10 x 30mm
IP Rating	IP67
Housing Material	ABS plastic
Sensing Method	Through-beam receiver
Operating Voltage	10-30 VDC
Number of Wires	4
Switching Output	NPN
Sensing Distance	25m
Operation Mode	Complementary light-on/dark-on
Switching Frequency	1 kHz
Light emission	Visible red
IO-Link Compatible	No
Connection	4-pin M8 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document