

LMR-133015 Cut Sheet



IDEM safety switch set, non-contact magnetic, (2) N.C. safety output(s), (1) N.O. monitoring output(s), 316 stainless steel housing, 88 x 25mm, pigtail, 32.8ft/10m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LMR-133015>

Technical Specifications

Brand	IDEM
Item	Safety switch set
Actuator Type	Non-contact magnetic
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.O.
IP Rating	IP67 IP69K
Housing Material	316 stainless steel
Housing Size	88 x 25mm
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	32.8ft/10m

Agency Approvals

UL Listed File #	E300466
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LMR-133015.pdf>
See store item page for other formats.