

LP15-1405 Cut Sheet



Flowline Switch-Tek guard capacitance liquid level switch, any orientation mount, 2.6in insertion length, polypropylene wetted parts, -40 to 176 deg F, 3/4in male NPT process connection, SPST relay, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LP15-1405>

Technical Specifications

Brand	Flowline
Series	Switch-Tek
Item	Level switch
Sensor Type	Guard capacitance
Media Type	Liquid
Mounting	Any orientation
Insertion Length	2.6in
Process Connection	3/4in male NPT
Wetted Parts	Polypropylene
Process Temperature	-40 to 176 deg F
Output	SPST relay, N.O./N.C. selectable
Operating Voltage	12-36 VDC
Electrical Connection	10ft 22AWG 4-conductor shielded cable
Jacket Material	Polypropylene

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document