

# LPCS12-24 Cut Sheet



SureMotion linear precision ground shaft, 1060 steel, RC60-65, 10RMS, 0.7495in diameter, 24in length. For use with 3/4in SureMotion bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPCS12-24>

## Technical Specifications

Brand	SureMotion
Item	Shaft
Shaft Type	Linear precision ground
Material	1060 steel
Hardness	RC60-65
Surface Finish	10RMS
Diameter	0.7495in
Length	24in
For Use With	3/4in SureMotion bearings

## Agency Approvals

RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/LPCS12-24.pdf>  
See store item page for other formats.