

# LPCS12-36 Cut Sheet



SureMotion linear precision ground shaft, 1060 steel, RC60-65, 10RMS, 0.7495in diameter, 36in length. For use with 3/4in SureMotion bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPCS12-36>

---

## Technical Specifications

<b>Brand</b>	SureMotion
<b>Item</b>	Shaft
<b>Shaft Type</b>	Linear precision ground
<b>Material</b>	1060 steel
<b>Hardness</b>	RC60-65
<b>Surface Finish</b>	10RMS
<b>Diameter</b>	0.7495in
<b>Length</b>	36in
<b>For Use With</b>	3/4in SureMotion bearings

---

## Agency Approvals

<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>