

LPD5-A-AC Cut Sheet



ProSense digital process meter, field mount, 100mm 5-digit red sunlight readable LED, current or voltage input, (2) 5A SPDT relays output, 100-240 VAC operating voltage, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPD5-A-AC>

Technical Specifications

Brand	ProSense
Item	Digital process meter
Mounting	Field
Display Type	100mm 5-digit red sunlight readable LED
Input	Current or voltage
Input Current Signal Range	+/- 20 mA
Input Voltage Signal Range	+/- 10 VDC
Output	(2) 5A SPDT relays
Operating Voltage	100-240 VAC
IP Rating	IP65

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LPD5-A-AC.pdf>
See store item page for other formats.