

LPPS18-1C-D10H Cut Sheet



AchieVe mechanical pressure switch, 3–10 psig set point, 1–2 psig deadband range, Buna-N sensing element, Buna-N seal(s), SPDT 5A, 1/8in male NPT process connection, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPPS18-1C-D10H>

Technical Specifications

Brand	AchieVe	Sensing Element Material	Buna-N
Item	Mechanical pressure switch	Seal Material	Buna-N
Media Type	Liquid, air, gases, oil, water and chemicals	Switching Output	SPDT 5A
Setpoint Range	3–10 psig	Process Connection	1/8in male NPT
Deadband Range	1–2 psig	NEMA Rating	4/13
Actuator Type	Diaphragm	Electrical Connection	4-pin M12 quick-disconnect
Wetted Parts	Buna-N, brass	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E320431
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LPPS18-1C-D10H.pdf>
See store item page for other formats.