

# LPPT25-20-2000H Cut Sheet



AchieVe pressure transmitter, 0 to 2000 psig range, +/- 1% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/4in male NPT process connection, 9-32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPPT25-20-2000H>

## Technical Specifications

<b>Brand</b>	AchieVe
<b>Item</b>	Pressure transmitter
<b>Pressure Range</b>	0 to 2000 psig
<b>Accuracy</b>	+/- 1% of full range
<b>Sensing Element Material</b>	Stainless steel
<b>Analog Output</b>	4-20 mA
<b>Process Connection</b>	1/4in male NPT
<b>Operating Voltage</b>	9-32 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Media Type</b>	Liquid and gases
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E311366
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/LPPT25-20-2000H.pdf>  
See store item page for other formats.