

LPPT25-20-5000H Cut Sheet



AchieVe pressure transmitter, 0 to 5000 psig range, +/-1% accuracy, stainless steel sensing element, 4-20 mA analog output, 1/4in male NPT process connection, 9 to 32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LPPT25-20-5000H>

Technical Specifications

Brand	AchieVe
Item	Pressure transmitter
Pressure Range	0 to 5000 psig
Accuracy	+/-1% of full range
Sensing Element Material	Stainless steel
Analog Output	4-20 mA
Process Connection	1/4in male NPT
Operating Voltage	9 to 32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Media Type	Liquid and gases
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	E311366
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LPPT25-20-5000H.pdf>
See store item page for other formats.