


LR-4020 Cut Sheet



AutomationDirect LR series line reactor, 460 VAC, 20hp, 3-phase, 27A, 3% impedance, input or output side. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR-4020>

Technical Specifications

Brand	AutomationDirect
Item	Line reactor
Series	LR
Voltage Rating	460 VAC
Horsepower Rating	20hp
Number of Phases	3
Amperage Rating	27A
Impedance	3%
Orientation	Input or output side
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LR-4020.pdf>
See store item page for other formats.