


LR2-20P2 Cut Sheet



AutomationDirect LR2 series line reactor, 208/240 VAC, 1/4hp, 3-phase, 3A, 3% impedance, input or output side. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR2-20P2>

Technical Specifications

Brand	AutomationDirect
Item	Line reactor
Series	LR2
Voltage Rating	208/240 VAC
Horsepower Rating	1/4hp
Number of Phases	3
Amperage Rating	3A
Impedance	3%
Orientation	Input or output side
For Use With	Multiple AC drives

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document