


# LR2-40P2 Cut Sheet



AutomationDirect LR2 series line reactor, 460 VAC, 1/4hp, 3-phase, 0.7A, 3% impedance, input or output side. For use with multiple AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR2-40P2>

---

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Line reactor
<b>Series</b>	LR2
<b>Voltage Rating</b>	460 VAC
<b>Horsepower Rating</b>	1/4hp
<b>Number of Phases</b>	3
<b>Amperage Rating</b>	0.7A
<b>Impedance</b>	3%
<b>Orientation</b>	Input or output side
<b>For Use With</b>	Multiple AC drives

---

## Agency Approvals

<b>UL Listed File #</b>	E197592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>