

LR4-202LJBW-RG Cut Sheet



Patlite LED signal tower, (2) tiers, 40mm diameter, red/green, permanent or flashing (60 fpm +/- 2 fpm) light function, (4) alarms, 24 VDC, NPN/PNP polarity, colored lens, 80mm body length, off-white, 360 degree viewing angle, pole mount, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-202LJBW-RG>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number of Pre-Assembled Tiers	2
Diameter	40mm
Light Color(s)	Red/green
Light Function	Permanent or flashing (60 fpm +/- 2 fpm)
Number of Alarms	4
Voltage Rating	24 VDC
Polarity	NPN/PNP
Lens Type	Colored

Body Length	80mm
Body Color	Off-white
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Loudness Decibel	85 dB at 1m
Tone Frequency	1 kHz to 43 kHz
Tone Type	(4) selectable
Touch to Acknowledge	No
Connector Type	Pigtail
Mounting	Pole
IP Rating	IP54

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LR4-202LJBW-RG.pdf>
See store item page for other formats.