

# LR4-2M2LJBW-RG Cut Sheet



Patlite LED signal tower, (2) tiers, 40mm diameter, red/green, permanent or flashing (60 fpm +/- 2 fpm) light function, (4) alarms, 100-240 VAC, colored lens, 150mm body length, off-white, 360 degree viewing angle, pole mount, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-2M2LJBW-RG>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Signal tower
<b>Bulb Type</b>	LED
<b>Number of Pre-Assembled Tiers</b>	2
<b>Diameter</b>	40mm
<b>Light Color(s)</b>	Red/green
<b>Light Function</b>	Permanent or flashing (60 fpm +/- 2 fpm)
<b>Number of Alarms</b>	4
<b>Voltage Rating</b>	100-240 VAC
<b>Lens Type</b>	Colored
<b>Body Length</b>	150mm

<b>Body Color</b>	Off-white
<b>Body Material</b>	Polycarbonate
<b>Tower Viewing Angle</b>	360 degree
<b>Loudness Decibel</b>	85 dB at 1m
<b>Tone Frequency</b>	1 kHz to 43 kHz
<b>Tone Type</b>	(4) selectable
<b>Touch to Acknowledge</b>	No
<b>Connector Type</b>	Pigtail
<b>Mounting</b>	Pole
<b>IP Rating</b>	IP54

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E215660
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/LR4-2M2LJBW-RG.pdf>  
See store item page for other formats.