

# LR4-2M2WJBW-RG Cut Sheet



Patlite LED signal tower, (2) tiers, 40mm diameter, red/green, permanent or flashing (60 fpm +/- 2 fpm) light function, (4) alarms, 100-240 VAC, colored lens, 150mm body length, off-white, 360 degree viewing angle, direct mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-2M2WJBW-RG>

## Technical Specifications

|                                      |  |
|--------------------------------------|--|
| <b>Brand</b>                         | Patlite                                  |
| <b>Item</b>                          | Signal tower                             |
| <b>Bulb Type</b>                     | LED                                      |
| <b>Number of Pre-Assembled Tiers</b> | 2  |
| <b>Diameter</b>                      | 40mm                                     |
| <b>Light Color(s)</b>                | Red/green                                |
| <b>Light Function</b>                | Permanent or flashing (60 fpm +/- 2 fpm) |
| <b>Number of Alarms</b>              | 4  |
| <b>Voltage Rating</b>                | 100-240 VAC                              |
| <b>Lens Type</b>                     | Colored                                  |
| <b>Body Length</b>                   | 150mm                                    |
| <b>Body Color</b>                    | Off-white                                |
| <b>Body Material</b>                 | Polycarbonate                            |
| <b>Tower Viewing Angle</b>           | 360 degree                               |
| <b>Loudness Decibel</b>              | 85 dB at 1m                              |
| <b>Tone Frequency</b>                | 1 kHz to 43 kHz                          |
| <b>Tone Type</b>                     | (4) selectable                           |
| <b>Touch to Acknowledge</b>          | No                                       |
| <b>Connector Type</b>                | Pigtail                                  |
| <b>Mounting</b>                      | Direct                                   |
| <b>IP Rating</b>                     | IP65                                     |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E215660                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |