

LR4-3M2LJNW-RYG Cut Sheet



Patlite LED signal tower, (3) tiers, 40mm diameter, red/amber/green, permanent light function, 100-240 VAC, colored lens, 150mm body length, off-white, 360 degree viewing angle, pole mount, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-3M2LJNW-RYG>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number Of Tiers	3
Diameter	40mm
Light Color(s)	Red/amber/green
Light Function	Permanent
Voltage Rating	100-240 VAC

Lens Type	Colored
Body Length	150mm
Body Color	Off-white
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	Pigtail
Mounting	Pole
IP Rating	IP54

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LR4-3M2LJNW-RYG.pdf>
See store item page for other formats.