

LR4-4M2LJNW-RYGB Cut Sheet



Patlite LED signal tower, (4) tiers, 40mm diameter, red/amber/green/blue, permanent light function, 100-240 VAC, colored lens, 150mm body length, off-white, 360 degree viewing angle, pole mount, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-4M2LJNW-RYGB>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number Of Tiers	4
Diameter	40mm
Light Color(s)	Red/amber/green/blue
Light Function	Permanent
Voltage Rating	100-240 VAC
Lens Type	Colored
Body Length	150mm
Body Color	Off-white
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	Pigtail
Mounting	Pole
IP Rating	IP54

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document