

# LR4-BW Cut Sheet



Patlite buzzer element, 85 dB at 1m, 2 kHz to 4 kHz tone frequency, (4) selectable tone(s), 24 VDC, polycarbonate housing, off-white, IP65. For use with LR4 series signal towers.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-BW>

## Technical Specifications

Brand	Patlite
Item	Buzzer element
Loudness Decibel	85 dB at 1m
Tone Frequency	2 kHz to 4 kHz
Tone Type	(4) selectable
Touch to Acknowledge	No
Number of Alarms	4
Voltage Rating	24 VDC
Housing Material	Polycarbonate
Color	Off-white
IP Rating	IP65
For Use With	LR4 series signal towers

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/LR4-BW.pdf>  
See store item page for other formats.