

LR4-E-G Cut Sheet



Patlite LED light element, 40mm diameter, green, permanent or flashing (60 fpm +/- 2 fpm) light function, 24 VDC, colored lens. For use with LR4 series signal towers.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-E-G>

Technical Specifications

Brand	Patlite
Item	Light element
Bulb Type	LED
Diameter	40mm
Light Color(s)	Green
Light Function	Permanent or flashing (60 fpm +/- 2 fpm)
Voltage Rating	24 VDC
Lens Type	Colored
For Use With	LR4 series signal towers

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LR4-E-G.pdf>
See store item page for other formats.