

# LR4-M2WJNW Cut Sheet



Patlite body unit, 40mm diameter, 100-240 VAC, NPN polarity, off-white, direct mount, IP65. For use with 40mm terminal elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-M2WJNW>

---

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Body unit
<b>Diameter</b>	40mm
<b>Voltage Rating</b>	100-240 VAC
<b>Polarity</b>	NPN
<b>Body Color</b>	Off-white
<b>Body Material</b>	Polycarbonate
<b>Mounting</b>	Direct
<b>IP Rating</b>	IP65
<b>For Use With</b>	40mm terminal elements

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E215660
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>