

LR4-M2WJNW Cut Sheet



Patlite body unit, 40mm diameter, 100-240 VAC, NPN polarity, off-white, direct mount, IP65. For use with 40mm terminal elements.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LR4-M2WJNW>

Technical Specifications

Brand	Patlite
Item	Body unit
Diameter	40mm
Voltage Rating	100-240 VAC
Polarity	NPN
Body Color	Off-white
Body Material	Polycarbonate
Mounting	Direct
IP Rating	IP65
For Use With	40mm terminal elements

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LR4-M2WJNW.pdf>
See store item page for other formats.