

LRR-M18PA-NMS-101 Cut Sheet



Contrinex photoelectric sensor, tubular, threaded, polarized retroreflective, visible red, 0.02-7m sensing distance, complementary light-on/dark-on, NPN, 4-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LRR-M18PA-NMS-101>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 27mm body
IP Rating	IP67
Housing Material	ABS plastic
Sensing Method	Polarized retroreflective
Operating Voltage	10-30 VDC
Number of Wires	4

Switching Output	NPN
Sensing Distance	0.02-7m
Operation Mode	Complementary light-on/dark-on
Switching Frequency	1.5 kHz
Light Emission (NP)	Visible red
IO-Link Compatible	No
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LRR-M18PA-NMS-101.pdf>
See store item page for other formats.