

LS50L11B Cut Sheet



Greenlee Gator knockout punch set, 12 pieces, 360-degree adjustable head, round, 1/2in conduit-2in conduit, 18 VDC, 2.0 Ah capacity, plastic case.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS50L11B>

Technical Specifications

Brand	Greenlee
Series	Gator
Item	Knockout punch set
Number of Pieces	12
Knockout Size	1/2in conduit-2in conduit
Punch Shape	Round
Bolt Size	7/16in and 3/4in
Head Type	360-degree adjustable
Maximum Punch Thickness	10ga mild steel
Operation Type	Battery operated
Application	Hole cutting
For Use On	Steel, plastic, stainless steel and non-ferrous metals

Set Includes	Includes (6) Conduit Slug-Buster punch & die (1/2in, 3/4in, 1in, 1-1/4in, 1-1/2in, 2in), (2) hydraulic draw bolt (7/16in, 3/4in), (1) 7-ton battery hydraulic driver, (1) 18V Li-ion 2.0Ah battery, (1) 120V AC Charger and (1) plastic case
Package Type	Plastic case
Dangerous Goods	Battery Installed: No, Packaging Instructions: 966, UN Number: UN3481, Hazard Type: Lithium Ion Batteries, Battery Type: Battery pack, Watt Hours: 36 and Replacement Battery: Makita BL1820B
Voltage	18 VDC
Capacity	2.0 Ah

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document