

LS7-302BWC9-RYGNN Cut Sheet



Patlite LED signal tower, (3) tiers, 70mm diameter, red/amber/green, permanent light function, (1) alarm, 24 VDC, NPN/PNP polarity, clear lens, 270mm body length, off-white, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-302BWC9-RYGNN>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number of Pre-Assembled Tiers	3
Diameter	70mm
Light Color(s)	Red/amber/green
Light Function	Permanent
Number of Alarms	1
Voltage Rating	24 VDC
Polarity	NPN/PNP
Lens Type	Clear
Body Length	270mm

Body Color	Off-white
Body Material	ABS plastic
Tower Viewing Angle	360 degree
Loudness Decibel	85 dB at 1m
Tone Frequency	2 kHz to 3 kHz
Tone Type	Continuous/intermittent
Touch to Acknowledge	No
Connector Type	8-pin M12 quick-disconnect
Mounting	Direct
IP Rating	IP69K
Application	High-temperature, high-pressure and washdown safe

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LS7-302BWC9-RYGNN.pdf>
See store item page for other formats.