

# LS7-302BWC9-RYGNN Cut Sheet



Patlite LED signal tower, (3) tiers, 70mm diameter, red/amber/green, permanent light function, (1) alarm, 24 VDC, NPN/PNP polarity, clear lens, 270mm body length, off-white, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-302BWC9-RYGNN>

## Technical Specifications

|                                      |   |
|--------------------------------------|---|
| <b>Brand</b>                         | Patlite   |
| <b>Item</b>                          | Signal tower                                      |
| <b>Bulb Type</b>                     | LED   |
| <b>Number of Pre-Assembled Tiers</b> | 3   |
| <b>Diameter</b>                      | 70mm  |
| <b>Light Color(s)</b>                | Red/amber/green                                   |
| <b>Light Function</b>                | Permanent   |
| <b>Number of Alarms</b>              | 1   |
| <b>Voltage Rating</b>                | 24 VDC  |
| <b>Polarity</b>                      | NPN/PNP   |
| <b>Lens Type</b>                     | Clear   |
| <b>Body Length</b>                   | 270mm   |
| <b>Body Color</b>                    | Off-white   |
| <b>Body Material</b>                 | ABS plastic                                       |
| <b>Tower Viewing Angle</b>           | 360 degree  |
| <b>Loudness Decibel</b>              | 85 dB at 1m                                       |
| <b>Tone Frequency</b>                | 2 kHz to 3 kHz                                    |
| <b>Tone Type</b>                     | Continuous/intermittent                           |
| <b>Touch to Acknowledge</b>          | No  |
| <b>Connector Type</b>                | 8-pin M12 quick-disconnect                        |
| <b>Mounting</b>                      | Direct  |
| <b>IP Rating</b>                     | IP69K   |
| <b>Application</b>                   | High-temperature, high-pressure and washdown safe |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E215660                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |