

LS7-302DWC9-RYGNN Cut Sheet



Patlite LED signal tower, (3) tiers, 70mm diameter, red/amber/green, permanent light function, 24 VDC, NPN/PNP polarity, clear lens, 230mm body length, dark gray, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-302DWC9-RYGNN>

Technical Specifications

Brand	Patlite	Lens Type	Clear
Item	Signal tower	Body Length	230mm
Bulb Type	LED	Body Color	Dark gray
Number Of Tiers	3	Body Material	ABS plastic
Diameter	70mm	Tower Viewing Angle	360 degree
Light Color(s)	Red/amber/green	Connector Type	8-pin M12 quick-disconnect
Light Function	Permanent	Mounting	Direct
Voltage Rating	24 VDC	IP Rating	IP69K
Polarity	NPN/PNP	Application	High-temperature, high-pressure and washdown safe

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LS7-302DWC9-RYGNN.pdf>
See store item page for other formats.