

LS7-302WC9-RYGNN Cut Sheet



Patlite LED signal tower, (3) tiers, 70mm diameter, red/amber/green, permanent light function, 24 VDC, NPN/PNP polarity, clear lens, 230mm body length, off-white, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-302WC9-RYGNN>

Technical Specifications

| | |
|------------------------|-----------------|
| Brand | Patlite |
| Item | Signal tower |
| Bulb Type | LED |
| Number Of Tiers | 3 |
| Diameter | 70mm |
| Light Color(s) | Red/amber/green |
| Light Function | Permanent |
| Voltage Rating | 24 VDC |
| Polarity | NPN/PNP |

| | |
|----------------------------|---------------------------------------------------|
| Lens Type | Clear |
| Body Length | 230mm |
| Body Color | Off-white |
| Body Material | ABS plastic |
| Tower Viewing Angle | 360 degree |
| Connector Type | 8-pin M12 quick-disconnect |
| Mounting | Direct |
| IP Rating | IP69K |
| Application | High-temperature, high-pressure and washdown safe |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E215660 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LS7-302WC9-RYGNN.pdf>
See store item page for other formats.