

# LS7-502BWC-RYGBC Cut Sheet



Patlite LED signal tower, (5) tiers, 70mm diameter, red/amber/green/blue/clear, permanent light function, (1) alarm, 24 VDC, NPN/PNP polarity, clear lens, 284mm body length, off-white, 360 degree viewing angle, direct mount, IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-502BWC-RYGBC>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Signal tower
<b>Bulb Type</b>	LED
<b>Number of Pre-Assembled Tiers</b>	5
<b>Diameter</b>	70mm
<b>Light Color(s)</b>	Red/amber/green/blue/clear
<b>Light Function</b>	Permanent
<b>Number of Alarms</b>	1
<b>Voltage Rating</b>	24 VDC
<b>Polarity</b>	NPN/PNP
<b>Lens Type</b>	Clear
<b>Body Length</b>	284mm
<b>Body Color</b>	Off-white
<b>Body Material</b>	ABS plastic
<b>Tower Viewing Angle</b>	360 degree
<b>Loudness Decibel</b>	85 dB at 1m
<b>Tone Frequency</b>	2 kHz to 3 kHz
<b>Tone Type</b>	Continuous/intermittent
<b>Touch to Acknowledge</b>	No
<b>Connector Type</b>	8-pin M12 quick-disconnect
<b>Mounting</b>	Direct
<b>IP Rating</b>	IP54

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E215660
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	C22.2 No.14
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>