

LS7-502BWC9-RYGBC Cut Sheet



Patlite LED signal tower, (5) tiers, 70mm diameter, red/amber/green/blue/clear, permanent light function, (1) alarm, 24 VDC, NPN/PNP polarity, clear lens, 270mm body length, off-white, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-502BWC9-RYGBC>

Technical Specifications

| | |
|--------------------------------------|----------------------------|
| Brand | Patlite |
| Item | Signal tower |
| Bulb Type | LED |
| Number of Pre-Assembled Tiers | 5 |
| Diameter | 70mm |
| Light Color(s) | Red/amber/green/blue/clear |
| Light Function | Permanent |
| Number of Alarms | 1 |
| Voltage Rating | 24 VDC |
| Polarity | NPN/PNP |
| Lens Type | Clear |
| Body Length | 270mm |

| | |
|-----------------------------|---|
| Body Color | Off-white |
| Body Material | ABS plastic |
| Tower Viewing Angle | 360 degree |
| Loudness Decibel | 85 dB at 1m |
| Tone Frequency | 2 kHz to 3 kHz |
| Tone Type | Continuous/intermittent |
| Touch to Acknowledge | No |
| Connector Type | 8-pin M12 quick-disconnect |
| Mounting | Direct |
| IP Rating | IP69K |
| Application | High-temperature, high-pressure and washdown safe |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E215660 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LS7-502BWC9-RYGBC.pdf>
See store item page for other formats.