

LS7-502DWC9-RYGBC Cut Sheet



Patlite LED signal tower, (5) tiers, 70mm diameter, red/amber/green/blue/clear, permanent light function, 24 VDC, NPN/PNP polarity, clear lens, 230mm body length, dark gray, 360 degree viewing angle, direct mount, IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LS7-502DWC9-RYGBC>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number Of Tiers	5
Diameter	70mm
Light Color(s)	Red/amber/green/blue/clear
Light Function	Permanent
Voltage Rating	24 VDC
Polarity	NPN/PNP
Lens Type	Clear
Body Length	230mm
Body Color	Dark gray
Body Material	ABS plastic
Tower Viewing Angle	360 degree
Connector Type	8-pin M12 quick-disconnect
Mounting	Direct
IP Rating	IP69K
Application	High-temperature, high-pressure and washdown safe

Agency Approvals

UL Listed File #	None
UL Recognized File #	E215660
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document