

# LSMM-172004 Cut Sheet



IDEM safety limit switch, brass plunger, (1) N.C. safety output(s), (1) N.O. monitoring output(s), snap action, die-cast zinc aluminum, pigtail, 6.5ft/2m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LSMM-172004>

## Technical Specifications

<b>Brand</b>	IDEM
<b>Item</b>	Safety limit switch
<b>Switch Type</b>	IEC
<b>Actuator Type</b>	Brass plunger
<b>Safety Output Type</b>	(1) N.C.
<b>Monitoring Output Type</b>	(1) N.O.
<b>Action</b>	Snap action
<b>Reset</b>	No
<b>Body Width</b>	35mm
<b>Material</b>	Die-cast zinc aluminum
<b>IP Rating</b>	IP67
<b>Connection</b>	Pigtail
<b>Conductor Size</b>	18 AWG
<b>Cable Length</b>	6.5ft/2m

## Agency Approvals

<b>UL Listed File #</b>	E258676
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>