

LSMM-172022 Cut Sheet



IDEM safety limit switch, plunger with brass roller and fixing nuts, (2) N.C. safety output(s), (1) N.O. monitoring output(s), slow action break before make, die-cast zinc aluminum, pigtail, 6.5ft/2m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LSMM-172022>

Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Plunger with brass roller and fixing nuts
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.O.
Action	Slow action break before make
Reset	No
Body Width	35mm
Material	Die-cast zinc aluminum
IP Rating	IP67
Connection	Pigtail
Conductor Size	18 AWG
Cable Length	6.5ft/2m

Agency Approvals

UL Listed File #	E258676
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document