

LSPM-170024 Cut Sheet



IDEM safety limit switch, plunger with brass roller and fixing nuts, (1) N.C. safety output(s), (1) N.O. monitoring output(s), snap action, polyester, pigtail, 6.5ft/2m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LSPM-170024>

Technical Specifications

Brand	IDEM
Item	Safety limit switch
Switch Type	IEC
Actuator Type	Plunger with brass roller and fixing nuts
Safety Output Type	(1) N.C.
Monitoring Output Type	(1) N.O.
Action	Snap action
Reset	No
Body Width	35mm
Material	Polyester
IP Rating	IP67
Connection	Pigtail
Conductor Size	18 AWG
Cable Length	6.5ft/2m

Agency Approvals

UL Listed File #	E258676
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LSPM-170024.pdf>
See store item page for other formats.