


LT-M-0130-S-L Cut Sheet

Gefran potentiometer linear position sensor, fixed slide, 130mm stroke, 32 x 33 x 193mm body, channel mount, 18mm DIN 43650 Form A.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LT-M-0130-S-L>

Technical Specifications

Brand	Gefran	Housing Size	32 x 33 x 193mm body
Item	Linear position sensor	Sensor Resolution	Infinite
Transducer Type	Potentiometer	Linearity	+/- 0.05%
Action	Fixed slide	Switching Cycles	25,000,000 cycles
Stroke	130mm	Mounting	Channel
Resistance	5k ohm	IP Rating	IP60
Head Type	M6	Connection	18mm DIN 43650 Form A
Head Material	Stainless steel	Number of Wires	4
Housing Material	Anodized aluminum	Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LT-M-0130-S-L.pdf>
See store item page for other formats.