

LTR-C23PA-PMK-101 Cut Sheet



Contrinex photoelectric sensor, rectangular, diffuse, visible red, 5–1200mm sensing distance, complementary light-on/dark-on, NPN, 1.5 kHz switching frequency, 20 x 10 x 30mm body, ABS plastic, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LTR-C23PA-PMK-101>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Rectangular
IP Rating	IP67
Application	Standard duty and food and beverage
Housing Size	20 x 10 x 30mm body
Housing Material	ABS plastic
Sensing Method	Diffuse
Operating Voltage	10–30 VDC
Switching Output	NPN
Sensing Distance	5–1200mm

Operation Mode	Complementary light-on/dark-on
Switching Frequency	1.5 kHz
Light Emission	Visible red
IO-Link Compatible	No
User Interface	Potentiometer
Cable Length	6.5ft/2m
Jacket Material	PVC
Connection	Pigtail
Number of Wires	4
Conductor Size	26 AWG
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/LTR-C23PA-PMK-101.pdf>
See store item page for other formats.