

LTR-D04MA-WXK-301 Cut Sheet

Contrinex photoelectric sensor, tubular, smooth, diffuse, visible red, 0-120mm sensing distance, light-on, NPN, teach-in wire, 1 kHz switching frequency, stainless steel housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LTR-D04MA-WXK-301>



Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Smooth
Housing Size	4mm diameter x 35.8mm body
IP Rating	IP67
Housing Material	Stainless steel
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Number of Wires	4

Switching Output	NPN
Sensing Distance	0-120mm
Sensitivity	Teach-in wire
Operation Mode	Light-on
Switching Frequency	1 kHz
Light Emission (NP)	Visible red
IO-Link Compatible	No
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	30 AWG

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LTR-D04MA-WXK-301.pdf>
See store item page for other formats.