

LTR-M12MA-PMK-101 Cut Sheet



Contrinex photoelectric sensor, tubular, threaded, diffuse, visible red, 5-800mm sensing distance, complementary light-on/dark-on, NPN, potentiometer, 1.5 kHz switching frequency, chrome-plated brass housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LTR-M12MA-PMK-101>

Technical Specifications

Brand	Contrinex
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	12mm diameter x 50mm body
IP Rating	IP67
Housing Material	Chrome-plated brass
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Number of Wires	4
Switching Output	NPN

Sensing Distance	5-800mm
Sensitivity	Potentiometer
Operation Mode	Complementary light-on/dark-on
Switching Frequency	1.5 kHz
Light Emission (NP)	Visible red
IO-Link Compatible	No
Cable Length	6.5ft/2m
Jacket Material	Carbon steel
Connection	Pigtail
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E239373
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LTR-M12MA-PMK-101.pdf>
See store item page for other formats.