

# LU10-1405 Cut Sheet



Flowline Switch-Tek ultrasonic liquid level switch, any orientation mount, 2.1in insertion length, polypropylene wetted parts, -40 to 176 deg F, 3/4in male NPT process connection, SPST relay, N.O./N.C. selectable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LU10-1405>

## Technical Specifications

<b>Brand</b>	Flowline
<b>Series</b>	Switch-Tek
<b>Item</b>	Level switch
<b>Sensor Type</b>	Ultrasonic
<b>Media Type</b>	Liquid
<b>Mounting</b>	Any orientation
<b>Insertion Length</b>	2.1in
<b>Process Connection</b>	3/4in male NPT
<b>Wetted Parts</b>	Polypropylene
<b>Process Temperature</b>	-40 to 176 deg F
<b>Output</b>	SPST relay, N.O./N.C. selectable
<b>Operating Voltage</b>	12-36 VDC
<b>Electrical Connection</b>	10ft 22AWG 4-conductor shielded cable
<b>Jacket Material</b>	Polypropylene

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	107382 (LR79326)
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>