

LU74-5004 Cut Sheet



Flowline EchoSwitch ultrasonic liquid level sensor, 18ft (5.5m) sensing range, 4-20 mA or (1) SPDT relay, (2) SPST-N.O. relays, 95-250 VAC operating voltage, LCD digital display with pushbuttons, 2in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LU74-5004>

Technical Specifications

Brand	Flowline
Series	EchoSwitch
Item	Level sensor
Sensor Type	Ultrasonic
Media Type	Liquid
Sensing Range	18ft (5.5m)
Output	4-20 mA or (1) SPDT relay, (2) SPST-N.O. relays
Operating Voltage	95-250 VAC
Housing Rating	NEMA 4X
Process Connection	2in male NPT
Electrical Connection	Screw terminals, (2) 1/2in female NPT
Display Type	LCD digital display with pushbuttons
Includes	Mounting gasket
Requires	Analog output requires separate 12-28 VDC power

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document