

# LV10-1301 Cut Sheet



Flowline Switch-Tek float liquid level switch, vertical mount, 4.3in insertion length, 1.0in diameter slosh shield float, polypropylene wetted parts, -40 to 194 deg F, 3/4in male NPT process connection, SPDT reed switch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LV10-1301>

## Technical Specifications

<b>Brand</b>	Flowline
<b>Item</b>	Level switch
<b>Series</b>	Switch-Tek
<b>Sensor Type</b>	Float
<b>Media Type</b>	Liquid
<b>Mounting</b>	Vertical
<b>Insertion Length</b>	4.3in
<b>Float</b>	1.0in diameter slosh shield
<b>Process Connection</b>	3/4in male NPT
<b>Wetted Parts</b>	Polypropylene
<b>Process Temperature</b>	-40 to 194 deg F
<b>Output</b>	SPDT reed switch
<b>Electrical Connection</b>	10ft 22AWG 3-conductor shielded cable
<b>Jacket Material</b>	Polypropylene

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/LV10-1301.pdf>  
See store item page for other formats.