

LZ12-1405 Cut Sheet



Flowline Switch-Tek vibration fork liquid level switch, any orientation mount, 2.3in insertion length, Ryton wetted parts, -40 to 176 deg F, 3/4in male NPT process connection, SPST relay, N.O./N.C. selectable, 10ft 24AWG 5-conductor shielded cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LZ12-1405>

Technical Specifications

Brand	Flowline
Item	Level switch
Series	Switch-Tek
Sensor Type	Vibration fork
Media Type	Liquid
Mounting	Any orientation
Insertion Length	2.3in
Process Connection	3/4in male NPT

Process Temperature	-40 to 176 deg F
Output	SPST relay, N.O./N.C. selectable
Operating Voltage	12-30 VDC
Wetted Parts	Ryton
Electrical Connection	10ft 24AWG 5-conductor shielded cable
Jacket Material	Polypropylene
Includes	DC NPN switch for maintenance alarm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LZ12-1405.pdf>
See store item page for other formats.