

M12A-08BMMM-PL8B05AD Cut SI



Amphenol connection cable, M12 axial male push-pull A-coded to pigtail, 8-pole, 30 V, 2 A, 24 AWG, PUR jacket, black, unshielded, 16.4 ft / 5 m cable length, IP68, sensor & signal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/M12A-08BMMM-PL8B05AD>

Technical Specifications

Brand	Amphenol
Item	Cable
Cable Type	Connection
Connection 1	M12 axial male push-pull A-coded
Connection 2	Pigtail
Number of Poles	8
Voltage Rating	30 V
Amperage Rating	2 A
Conductor Size	24 AWG

Jacket Material	PUR
Jacket Color	Black
Shield Type	Unshielded
Cable Length	16.4 ft / 5 m
IP Rating	IP68
Application	Sensor & signal
Additional Information	Backwards compatible with all M12x1.0 female connectors meeting the IEC standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	E318730
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/M12A-08BMMM-PL8B05AD.pdf>
See store item page for other formats.