

M2420HPLSL Cut Sheet



AttaBox MachoBox series enclosure, NEMA 1/3/3R/4/4X/12/13, 24 x 20 x 10in (HxWxD), fiberglass reinforced polyester, Pantone 428 C glacier gray, single-door, slotted twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/M2420HPLSL>

Technical Specifications

Brand	AttaBox
Item	Enclosure
Series	MachoBox
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3/3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Height	24in
Nominal Enclosure Width	20in
Nominal Enclosure Depth	10in
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Pantone 428 C glacier gray
Cover Type	Single-door
Latch Type	Slotted twist-lock latch
Number Of Latches	1
Secondary Latch Type	Stainless steel quick-release latch
Number Of Secondary Latches	3
Padlockable	Yes

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/M2420HPLSL.pdf>
See store item page for other formats.