

MBT16M-38R Cut Sheet



NITRA fitting, branch tee, (2) 16mm tube to R3/8 BSPT connection(s), thermoplastic (PBT) body, nickel-plated brass threads. Package of 3.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MBT16M-38R>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Gender	Male
Fitting Type	Branch tee
Fitting Function	Rotating
Body Material	Thermoplastic (PBT)
Thread Material	Nickel-plated brass
Thread Sealant	Yes
Connection	(2) 16mm push-to-connect and R3/8 BSPT
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	3
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document