

MBT38-14N-B Cut Sheet



NITRA pneumatic push-to-connect fitting, male, branch tee, rotating, nickel-plated brass body, nickel-plated brass threads, thread sealant, (2) 3/8in push-to-connect to 1/4in NPT. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MBT38-14N-B>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Gender	Male
Fitting Type	Branch tee
Fitting Function	Rotating
Body Material	Nickel-plated brass

Thread Material	Nickel-plated brass
Thread Sealant	Yes
Connection	(2) 3/8in push-to-connect and 1/4in NPT
Operating Pressure	0 to 300 psi
Operating Temperature	0 to 175 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MBT38-14N-B.pdf>
See store item page for other formats.