

MBVPE-11-WNL Cut Sheet



Bimed pressure relief vent plug, M20 x 1.5mm thread type, polyamide, light gray, 2,000 mL/min @ 70 mBar (1 psi), IP67 IP68. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MBVPE-11-WNL>

Technical Specifications

| | |
|---------------------------------|--------------------------------|
| Brand | Bimed |
| Item | Pressure relief vent plug |
| Thread Type | M20 x 1.5mm |
| Thread Length | 10mm |
| Material | Polyamide |
| Color | Light gray |
| Free Airflow | 2,000 mL/min @ 70 mBar (1 psi) |
| Water Intrusion Pressure | 0.5 bar (7 psi) |
| IP Rating | IP67 IP68 |
| Operating Temperature | -20 to +100 deg C |
| Quantity per Pack | 2 |
| Includes | Washer and lock nut |
| Additional Information | Use 24mm wrench size |

Agency Approvals

| | |
|--------------------|----------------------------------------|
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MBVPE-11-WNL.pdf>
See store item page for other formats.