

MBVPG-13-WNL Cut Sheet



Bimed pressure relief vent plug, M12 x 1.5mm thread type, polyamide, light gray, 417 mL/min @ 70 mBar (1 psi), IP67 IP68 IP69K. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MBVPG-13-WNL>

Technical Specifications

Brand	Bimed
Item	Pressure relief vent plug
Thread Type	M12 x 1.5mm
Thread Length	10mm
Material	Polyamide
Color	Light gray
Free Airflow	417 mL/min @ 70 mBar (1 psi)
Water Intrusion Pressure	0.5 bar (7 psi)
IP Rating	IP67 IP68 IP69K
Operating Temperature	-20 to +100 deg C
Quantity per Pack	2
Includes	Washer and lock nut
Additional Information	Use 17mm wrench size

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MBVPG-13-WNL.pdf>
See store item page for other formats.